

Constant Coefficient Multiplier (Pipelined)

July 17, 1998



Xilinx Inc. 2100 Logic Drive San Jose, CA 95124

Phone: +1 408-559-7778
Fax: +1 408-559-7114
E-mail: coregen@xilinx.com
URL: www.xilinx.com

Features

- · Pipelined construction for increased throughput
- Multiplies a variable A times a constant B
- The A value can range from 4 to 32 bits
- The **B** value can range from 2 to 26 bits
- Independent A and B word size
- Independent selection of signed and unsigned data format for each operand
- Full precision output
- Supports 2's complement signed and unsigned magnitude numbers
- The inputs are not registered, but the outputs are registered
- Drop-in modules for the XC4000E, EX, XL, XV and Spartan families
- High performance and density guaranteed through Relational Placed Macro (RPM) mapping and placement technology
- · Available in Xilinx CORE Generator

Functional Description

This parameterized module multiplies an N-bit wide variable times an M-bit fixed coefficient and produces an N+M bit result. The coefficient multiplication tables are stored in distributed ROM-based look-up tables (LUTs), taking advantage of the FPGA look-up table architecture. It is an efficient, high speed, parallel implementation.

The variable and constant bit widths can be set independently, allowing the user to multiply different word widths together. The module automatically adjusts the signed and unsigned data to properly handle different sizes.

The variable and constant can be independently selected to be 2's complement signed or unsigned magnitude-only values. Note that the module will automatically handle a **Product Specification**

signed times an unsigned number, two signed numbers, or two unsigned numbers.

The Constant Coefficient Multiplier (KCM) is used where the value of an incoming variable needs to be multiplied by a number that does not change, a constant. This is often the case in scaling functions. FIR filters. IIR filters. etc.

Pinout

Port names for the schematic symbol are shown in Figure 1 and described in Table 1.




Figure 1: Block Diagram

Table 1: Core Signal Pinout

Signal	Signal Direction	Description
A[n:0]	Input	PARALLEL DATA IN – A operand.
С	Input	CLOCK – with the exception of asynchronous control inputs (where applicable), control and data inputs are captured, and new output data formed on rising clock transitions.
PROD[m+n+1:0]	Output	PARALLEL DATA OUT - product result.

CORE Generator Parameters

The CORE Generator parameterization window for this macro is shown in Figure 2. The parameters are as follows:

- Component Name: Enter a name for the component.
- A Width: Select an input bit width from the pull-down

- menu for the variable width. The valid range is 4 to 32.
- Signed Input Data: Set the sign of the variable to Signed or Unsigned.
- Coefficient Width: Select an input bit width from the pull-down menu for the constant width. The valid range is 2 to 26.
- · Coefficient: Enter the value of the desired constant.
- Signed Coefficient: Set the sign of the constant to Signed or Unsigned.
- Radix: Hexadecimal or Decimal representation of the constant.




Figure 2: Parameterization Window

Multiplier Latency

The total latency (number of clocks required to get the first output) is a function of the width of variable **A**. Table 2 shows the latency for the possible bit widths of **A**.

Table 2: Multiplier Latency

A Data Width	Latency (# Clocks)
4 to 5 bits	1
6 to 10 bits	2
11 to 17 bits	3
18 to 32 bits	4

Core Resource Utilization

Table 3 shows the resource utilization for some available bit widths.

Ordering Information

This macro comes free with the Xilinx CORE Generator. For additional information contact your local Xilinx sales representative, or e-mail requests to coregen@xilinx.com.

Table 3: Constant Coefficient Multiplier Characterization Table

4 4 4 4,1 228 152 175 4 8 6 6,1 210 147 170 4 16 10 10,1 169 1118 141 4 20 12 12,1 172 120 131 4 24 14 14,1 161 115 121 4 26 15 15,1 158 110 121 8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 8 21 7,3 117 77 100 8 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7	A Width	B Width	CLB Count	Area Required for RPM (Rows, Columns)	4000XL-08 (Advanced) MHz	4000XL-09 MHz	4000XL-3 MHz	Spartan -4 (Advanced) MHz
4 16 10 10,1 169 118 141 4 20 12 12,1 172 120 131 4 24 14 14,1 161 115 121 4 26 15 15,1 158 110 121 8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 87	4	4	4	4,1		228	152	175
4 20 12 12,1 172 120 131 4 24 14 14,1 161 115 121 4 26 15 15,1 158 110 121 8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81	4	8	6	6,1		210	147	170
4 24 14 14,1 161 115 121 4 26 15 15,1 158 110 121 8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 87 80 52 64 16 24 111 17,7	4	16	10	10,1		169	118	141
4 26 15 15,1 158 110 121 8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 24 111 17,7	4	20	12	12,1		172	120	131
8 4 15 5,3 126 83 110 8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 4 <t< td=""><td>4</td><td>24</td><td>14</td><td>14,1</td><td></td><td>161</td><td>115</td><td>121</td></t<>	4	24	14	14,1		161	115	121
8 8 21 7,3 117 77 100 8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4	4	26	15	15,1		158	110	121
8 16 33 11,3 101 66 81 8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149	8	4	15	5,3		126	83	110
8 20 39 13,3 94 62 76 8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173	8	8	21	7,3		117	77	100
8 24 45 15,3 83 54 70 8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197	8	16	33	11,3		101	66	81
8 26 48 16,3 83 55 68 16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 <td>8</td> <td>20</td> <td>39</td> <td>13,3</td> <td></td> <td>94</td> <td>62</td> <td>76</td>	8	20	39	13,3		94	62	76
16 4 41 7,7 115 74 96 16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32	8	24	45	15,3		83	54	70
16 8 55 9,7 105 68 88 16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 24 197 17,12 86 79 52 64 24 24 26 209 18,12 83 76 50 <t< td=""><td>8</td><td>26</td><td>48</td><td>16,3</td><td></td><td>83</td><td>55</td><td>68</td></t<>	8	26	48	16,3		83	55	68
16 16 83 13,7 88 58 74 16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 <td>16</td> <td>4</td> <td>41</td> <td>7,7</td> <td></td> <td>115</td> <td>74</td> <td>96</td>	16	4	41	7,7		115	74	96
16 20 97 15,7 81 53 68 16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 24 29 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 <td>16</td> <td>8</td> <td>55</td> <td>9,7</td> <td></td> <td>105</td> <td>68</td> <td>88</td>	16	8	55	9,7		105	68	88
16 24 111 17,7 87 80 52 64 16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45	16	16	83	13,7		88	58	74
16 26 118 18,7 86 78 51 62 24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	16	20	97	15,7		81	53	68
24 4 77 7,12 108 71 89 24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	16	24	111	17,7	87	80	52	64
24 8 101 9,12 103 67 86 24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	16	26	118	18,7	86	78	51	62
24 16 149 13,12 87 56 73 24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	4	77	7,12		108	71	89
24 20 173 15,12 82 54 68 24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	8	101	9,12		103	67	86
24 24 197 17,12 86 79 52 64 24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	16	149	13,12		87	56	73
24 26 209 18,12 83 76 50 60 32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	20	173	15,12		82	54	68
32 4 101 11,15 89 57 73 32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	24	197	17,12	86	79	52	64
32 8 131 13,15 84 54 69 32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	24	26	209	18,12	83	76	50	60
32 16 191 17,15 81 75 48 60 32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	32	4	101	11,15		89	57	73
32 20 221 19,15 77 71 45 55 32 24 251 21,15 68 43 53	32	8	131	13,15		84	54	69
32 24 251 21,15 68 43 53	32	16	191	17,15	81	75	48	60
	32	20	221	19,15	77	71	45	55
32 26 266 22,15 66 42 44	32	24	251	21,15		68	43	53
	32	26	266	22,15		66	42	44

To achieve the performance documented in this table, it may be necessary to specify a TIMESPEC (timing specification) PERIOD constraint appropriate to meet the documented frequency.

Parameter File Information

Parameter Name	Type	Notes
Component_Name	String	
A_Width	Integer	4 - 32
Coef_Width	Integer	2 - 26
Signed_Input_Data	Boolean	True/False
Signed_Coefficient	Boolean	True/False
Coefficient	Integer	